

**TECHSPEC® Compression Springs (2pk)**



#86-838

Stock **#86-838 8 In Stock**

1  MRP ₹1,237

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing

Qty 1+	₹1,237 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Regulatory Compliance**

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

United States

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,

## Product Details

- Compact Design with Built-In Translation Assembly
- Configurable for ½" or 1" Travel
- **Accepts Micrometers with 3/8" Shank**
- Step-by-Step Assembly Instructions [Available](#)

TECHSPEC® Cage System Linear Translation Assemblies are used to add linear translation to a TECHSPEC Optical Cage System setup. The built-in translation assembly enables coarse positioning along the cage rods. Once fixed to the cage rods, fine translation can be done using a micrometer drive. By adding additional springs and replacing the 3mm x 50mm rods ([#85-470](#)) with two 3mm x 75mm ([#86-847](#), sold separately), the ½" standard travel can be extended to 1". TECHSPEC Cage System Linear Translation Assemblies are available in two options: simple translation utilizes 6mm rods and standard plates, while ball bearing translation utilizes ball bearing slides for low-friction translation.

**Note:** [Micrometer/drive mechanism](#) and [6mm Support Rods](#) sold separately.

## Technical Information

Description	Quantity	Feature	Stock No.
Micrometer Mount Kit	1 Required	Micrometer Holder	<a href="#">#85-618</a>
		Protective Steel Plate	
		<a href="#">#86-838</a> Compression Springs (2pk)	
25mm Standard Cage Plate, M6	2 Required*	One plate is used for travel and second plate is fixed	<a href="#">#85-632</a>
30mm Standard Cage Plate, M6			<a href="#">#85-630</a>
25mm Standard Cage Plate, ¼-20			<a href="#">#85-633</a>
30mm Standard Cage Plate, ¼-20			<a href="#">#85-631</a>
Micrometer or Actuator	1 Required	Choose based on type, travel, and graduation	<a href="#">Customer Selected</a>
Shaft Collar (2pk)	1 Optional	Can be used instead of a fixed plate	<a href="#">#86-845</a>
Compression Springs (2pk)	1 Optional	Used to extend travel range to 1"	<a href="#">#86-838</a>

\***Note:** Only 1 required if Shaft Collars are used.

Description	Quantity	Feature	Stock No.
Translation Assembly Kit	1 Required	<a href="#">#85-618</a> Micrometer Mount Kit	<a href="#">#86-847</a>
		<a href="#">#85-620</a> Travel Bearing Plate	
		<a href="#">#85-619</a> Fixed Bearing Plate	
		<a href="#">#85-686</a> Linear Bearing Bushings (2pk)	
		<a href="#">#85-471</a> 3mm Dia x 75mm Length Rod (x2)	
Micrometer or Actuator	1 Required	Choose based on type, travel, and graduation	<a href="#">Customer Selected</a>
Compression Springs (2pk)	1 Optional	Used to extend travel range to 1"	<a href="#">#86-838</a>

Type	Travel	Graduation	Stock No.
Micrometer Drive	0.5"	0.001"	<a href="#">#58-660</a>
Micrometer Drive	25mm	0.01mm	<a href="#">#58-663</a>