

[See all 2 Products in Family](#)

## E-Series Jaw Clamp Kinematic Mount



E-Series Jaw Clamp Kinematic Mount (#17-243)

Stock **#17-243** **4 In Stock**

MRP ₹26,131

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹26,131 each
Qty 10+	₹24,839 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Adjustable - Tip-Tilt **Type:**

Circular **Type of Optics:**

2 **Number of Adjustment Screws:**

#### Physical & Mechanical Properties

40 **Clear Aperture CA (mm):**

**Construction:**  
Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings

±3.5 **Fine Tilt Angle (°):**

±3.5 **Fine Tip Angle (°):**

0.25 **Adjustment Screw Pitch (mm):**

2 **Min. Thickness of Compatible Optics (mm):**

38.10 **Optical Axis Height (mm):**

## Threading & Mounting

4.00 - 40.00 **Size of Compatible Optics (mm):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Taiwan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Essential Mount for Experiments and OEM System
- Compatible with 3–38.1mm Rectangular Optics
- Compatible with 4–40mm Diameter Optics
- M6 x 0.25 (101.6 TPI) Adjustment Screws

E-Series Adjustable Size Kinematic Optical Mounts are ideal for integrating a range of round, rectangular, and square optical components. These kinematic mounts offer many features essential for applications in R&D, prototyping, and OEM system integration. Wide clear apertures enhance compatibility for both reflective optics like mirrors and transmissive optics like beamsplitters, filters, and cylinder lenses. The two M6 x 0.25 (101.6 TPI) adjustment screws provide smooth movement and can be driven by hand or by Allen key (2mm key size) for tip and tilt optical adjustment and alignment ( $\pm 3.5^\circ$ ). The adjustment screw knobs are removable to create a more compact form factor. E-Series Adjustable Size Kinematic Optical Mounts are compatible with M4, 8-32, and M6 x 1.0 hardware for increased mounting versatility and direct compatibility with [TECHSPEC® Metric Stainless Steel Mounting Posts](#) and [Pedestal Posts](#).

**Note:** #17-242 has an optical axis height of 38.1mm when mounting a 25.4mm optical component. #17-243 has a constant 38.1mm optical axis height when mounting any compatible sized optical component.