

Green, UltraSeal Washdown Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity UltraSeal Washdown Spot Lights

Stock #21-972 CLEARANCE **1 In Stock**

1 - + **MRP ₹1,16,072**

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty	₹1,16,072
1+	each
Need More?	Request Quote

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Spec Sheets:pdf
eDrawing:eprt	
EO Spec Sheet	Download All

Note: This item requires accessories for use | [Learn More](#)

General

Model Number:	SL316M-530IC	LED Lifetime (hours):	50,000
Number of LEDs:	25	Type of Illumination:	LED Illuminator
Manufacturer:	Advanced Illumination	Geometry:	Spot Light
Illumination Mode:	Constant		

Physical & Mechanical Properties

Weight (g):	290
--------------------	-----

Optical Properties

Color:	Green	Wavelength (nm):	530
---------------	-------	-------------------------	-----

Hardware & Interface Connectivity

Connector:	Flying Leads	Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855
Length of Cable (m):	2		

Environmental & Durability Factors

Operating Temperature (°C): 0 to +60

Regulatory Compliance

Certificate of Conformance: [View](#)

Country of Origin: United States

Imported By: Edmund Optics India Private Limited
267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- IP69K Certified for Extreme Washdown Environments
- Ideal for Hygienic and Aseptic Manufacturing Applications
- Intensity of Over 60,000 Lux at 300mm Working Distance

Advanced Illumination High Intensity UltraSeal Washdown Spot Lights are ideal for extreme environments including high pressure steam cleaning and prolonged liquid immersion. Available in five colors, these spot lights feature high intensity output and consistent uniformity. These spot lights are IP69K certified and their proprietary nickel finish ensures better thermal conductivity than stainless steel while the sealed design reduces the potential for material buildup and improves cleanability. Advanced Illumination High Intensity UltraSeal Washdown Spot Lights can be used in hygienic inspection environments, aseptic manufacturing, and food and beverage applications.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	24V Power Supply with Tinned Leads		#66-855	₹10,089 Request Quote	20+ In Stock <input type="text" value="1"/>

Related Products



Advanced Illumination UltraSeal Washdown Bar Lights



Advanced Illumination High Intensity In-Line Lights



Cw Series Fixed Focal Length Lenses



IDS Imaging uEye+ FA IP65/67 PoE Cameras