

[See all 23 Products in Family](#)

# INFINITUBE FM Nikon CFI60 Objective Adapter (M25)

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock #58-315 **1 In Stock**

MRP ₹11,788

**Price inclusive of all taxes**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹11,788 each                  |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

## Regulatory Compliance

**Compliant** RoHS 2015:

**Compliant** Reach 224:

**View** Certificate of Conformance:

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000


## Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FM Systems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ #58-310 or #58-309) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FM Systems can also be configured for in-line illumination with attachments. The first in-line attachment (#58-313) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment (#58-312) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

**Note:** [Standard system](#) for 2/3" sensors still available.

## Technical Information



| System Includes                              | Stock No.               |
|--|-------------------------|
| InfiniTube In-Line Assembly Unit             | <a href="#">#58-311</a> |
| Hitachi KP-D20B Camera                       | <a href="#">#55-837</a> |
| 15.1" Diagonal LCD Monitor (US version only) | <a href="#">#56-522</a> |
| Y-C Cable (6 ft.)                            | <a href="#">#39-255</a> |
| Mitutoyo/Achrovid™ Objective Adapter         | <a href="#">#58-316</a> |
| M-150 Fiber Optic Illuminator                | <a href="#">#55-718</a> |
| Fiber Optic Light Guide (48" L)              | <a href="#">#39-367</a> |
| Fiber Optic Adapter                          | <a href="#">#38-944</a> |
| Standard Boom Stand                          | <a href="#">#54-120</a> |
| Rack & Pinion Mounting Plate                 | <a href="#">#54-123</a> |
| C-Clamp with 1/4-20 Mounting Hole            | <a href="#">#57-788</a> |