

TECHSPEC<sup>®</sup> M30.5 x 0.5 Mount for 25mm Diameter Filters



M30.5 x 0.5 Mount for 25mm Diameter Filters, #65-801

Stock **#65-801** 9 In Stock

-

1

+

₹4,048

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹4,048 each                   |
| Qty 10+        | ₹3,639 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Physical & Mechanical Properties  |                         |
|-----------------------------------|-------------------------|
| 22.0                              | Clear Aperture CA (mm): |
| 33.5                              | Outer Diameter (mm):    |
| 9.20                              | Thickness (mm):         |
| Black Anodized Aluminum (6061-T6) | Construction:           |

Threading & Mounting

|                                                      |                                      |
|------------------------------------------------------|--------------------------------------|
| M30.5 x0.50                                          | Filter Thread:                       |
| 6.5 Maximum                                          | Thickness of Compatible Optics (mm): |
| M30.5 x0.5 / M30.5 x0.5 (Male Thread/ Female Thread) | Mount:                               |

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| Compliant                           | Reach 209:                  |
| View                                | Certificate of Conformance: |
| China                               | Country of Origin:          |
| Edmund Optics India Private Limited | Importer:                   |

Product Details

- Specially Designed to Hold 25/25.4mm and 50/50.8mm Diameter Filters
  - Accommodate up to 7mm Thicknesses
  - Choose from our Full Selection of 25mm or 50mm Diameter Filters
  - [Premounted Edge Filters](#) and [Neutral Density Filters](#) Available
- TECHSPEC® Machine Vision Filter Mounts for 25 and 50mm Diameter Filters are designed to hold 25/25.4mm and 50/50.8mm diameter filters, enabling our full selection of [filters](#) to be used in imaging systems. Whether your application requires a unique bandpass, edge, notch, or neutral density filter, you can now easily attach any of our standard filter designs to the front of most imaging lenses. TECHSPEC® Machine Vision Filter Mounts for 25 and 50mm Diameter Filters have been designed to accommodate up to 7mm of filter thickness, making it easy to stack multiple [Hoya Absorptive Neutral Density Filters](#) to achieve custom optical densities. Even many of our [Hard Coated Bandpass Interference Filters](#) can now be easily integrated into imaging applications. These filters are constructed of black anodized aluminum and are available in various sizes of filter threads.
- [#65-800](#) is an ideal accessory to our family of [TECHSPEC® C Series Fixed Focal Length Lenses](#), and [#65-801](#) is an ideal accessory to the [Megapixel Fixed Focal Length Lenses](#) and [Schneider Compact VIS-NIR Lenses](#). The 50/50.8mm diameter filter mounts are ideal accessories for our large format imaging lenses, including our [1.1" HP Series Fixed Focal Length Lenses](#) and [TECHSPEC® LF Series Fixed Focal Length Lenses](#).