

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 13775 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-375** **1 In Stock**

MRP ₹13,063

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹13,063 each
Qty 5-11	₹11,756 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

General	
0.34	Size (oz):
13775	Norland Number:
4 months	Shelf Life:
	Type:

Barrel

Bonding glass to glass **Typical Applications:**

Contains 10g of adhesive **Note:**

## Optical Properties

1.3775 **Index of Refraction ( $n_d$ ):**

315 - 450 **Absorption Range (nm):**

## Material Properties

Good **Glass Bonding:**

Good **Metal Bonding:**

Good **Plastic Bonding:**

4000 **Viscosity (cps):**

Glass to Glass **Bonding Type:**

6 **Energy for Full Cure ( $J/cm^2$ ):**

## Environmental & Durability Factors

Soft **Durability:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 251:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.