

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NOA 139 Dispensing Barrel (3cc)

See More by [Norland](#)



Preloaded Norland Optical Adhesive Syringes



Stock #15-694 **2 In Stock**

- 1 + MRP ₹4,195

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-11	₹4,195 each
Qty 12-19	₹3,781 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Size (oz):  
0.1

Norland Number:  
139

Shelf Life:

4 months

Barrel

Type:

**Typical Applications:**  
Low viscosity adhesive for bonding glass or plastic.

**Note:**  
Contains 2g of adhesive

## Optical Properties

**Index of Refraction ( $n_d$ ):**  
1.39 @ 589nm

**Absorption Range (nm):**  
315 - 450

## Material Properties

**Glass Bonding:**  
Excellent

**Metal Bonding:**  
Good

**Plastic Bonding:**  
Good

**Viscosity (cps):**  
865

**Bonding Type:**  
Glass to Glass

**Energy for Full Cure ( $J/cm^2$ ):**  
6

## Environmental & Durability Factors

**Durability:**  
Flexible

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 251:**  
[Compliant](#)

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.