

TECHSPEC<sup>®</sup>Optical Component Kit



Stock #55-486 1 In Stock

-

1

+

 ₹1,47,900

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹1,47,900 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Optical Kit

Contents of Kit:

See Technical Information Tab

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

Product Details

- Ideal for Prototyping
- Matched to Mechanical Components
- Note: Potential change of packaging

A complete kit of precision optical components in stepped increments of focal length for systematic evaluation of optical system designs. Optics fit the mechanical components in the [C-Mount Component Kit](#) and can be found as individual components within our online catalog by following the links below.

**Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

Technical Information

| List of Components                                       | Quantity | Stock No.               |
|----------------------------------------------------------|----------|-------------------------|
| Cylindrical Lens - 12.5mm Diameter x 12.5mm FL           | 1        | <a href="#">#46-193</a> |
| Cylindrical Lens - 12.5mm Diameter x 25mm FL             | 1        | <a href="#">#46-194</a> |
| Cylindrical Lens - 12.5mm Diameter x 50mm FL             | 1        | <a href="#">#46-195</a> |
| Cylindrical Lens - 25 x 50mm, 25mm FL                    | 1        | <a href="#">#46-020</a> |
| Cylindrical Lens - 25 x 50mm, 50mm FL                    | 1        | <a href="#">#46-021</a> |
| Aspheric Condenser - 12.7mm Diameter x 15mm FL           | 1        | <a href="#">#43-370</a> |
| Ball Lens - 3mm Diameter                                 | 1        | <a href="#">#43-711</a> |
| Ball Lens - 5mm Diameter                                 | 1        | <a href="#">#43-712</a> |
| Rod Lens - 3mm Diameter x 6mm L                          | 1        | <a href="#">#54-088</a> |
| Rod Lens - 5mm Diameter x 10mm L                         | 1        | <a href="#">#54-090</a> |
| Drum Lens - 2.4mm x 3.0mm                                | 1        | <a href="#">#45-549</a> |
| GRIN Lens - 1.8mm Dia. x 0.0mm WD                        | 1        | <a href="#">#64-519</a> |
| Right Angle Prism - 10mm                                 | 1        | <a href="#">#32-330</a> |
| Right Angle Prism - 20mm                                 | 1        | <a href="#">#32-334</a> |
| Silvered Corner Cube - 25.4mm Diameter                   | 1        | <a href="#">#45-187</a> |
| Wedge Prism - 25mm Diameter                              | 1        | <a href="#">#45-557</a> |
| Equilateral Prism - 15mm                                 | 1        | <a href="#">#47-276</a> |
| Dove Prism- 15mm x 64mm                                  | 1        | <a href="#">#32-553</a> |
| Cube Beamsplitter - 10mm Sq., 50R/50T                    | 1        | <a href="#">#32-601</a> |
| Cube Beamsplitter - 20mm Sq., 50R/50T                    | 1        | <a href="#">#32-504</a> |
| Plate Beamsplitter - 35mm Sq., 30R/70T                   | 1        | <a href="#">#45-324</a> |
| Plate Beamsplitter - 35mm Sq., 70R/30T                   | 1        | <a href="#">#45-326</a> |
| Broadband Hybrid Diffuser - 12.5mm Diameter              | 1        | <a href="#">#36-610</a> |
| Ground Glass Diffuser - 15mm Diameter                    | 1        | <a href="#">#45-652</a> |
| First Surface Mirror - Protected Aluminum, 35mm Sq.      | 1        | <a href="#">#45-519</a> |
| First Surface Mirror - Protected Gold, 35mm Sq.          | 1        | <a href="#">#45-520</a> |
| Hexagonal Light Pipe - 4mm Aperture, 25mm Length High NA | 1        | <a href="#">#63-082</a> |