

[See all 65 Products in Family](#)

## 76.2mm Pedestal Post and Clamping Fork, Metric, 5 Pack



Pedestal Post

Stock **#17-507** CLEARANCE CONTACT US

MRP ₹20,385

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹20,385 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric **Type:**

5X#15-843, 5X#15-859 **Contents of Kit:**

With M6x1.0 screw holes on the base **Note:**

Pedestal Post **Function:**

### Physical & Mechanical Properties

76.20	<b>Length (mm):</b>
Stainless Steel	<b>Construction:</b>
0.31	<b>Weight (kg):</b>
25.4	<b>Post Diameter (mm):</b>
31.5	<b>Base Diameter (mm):</b>
<b>Threading &amp; Mounting</b>	
M4x0.7	<b>Mounting Threads:</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 233:</b>
Taiwan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>




## Product Details









- 1" Diameter Posts with Metric and English Mounting Hole Options
- Stainless Steel Construction for High Stability
- 0.5" - 4.0" Heights Available
- Refer to the Technical Information Tab to Find the Right Adapter for your Optical Mount and Application

Pedestal Posts and Accessories offer a stable way to mount optical components to a lab table with a consistent mounting height, providing predictable and repeatable mounting of components within an optical system. A variety of pedestal extenders and shim plates are available to ensure that the optical axis height is consistent for all mounted components. Pedestal Posts feature M4 x 0.7 or 8-32 tapped holes on the top surface, compatible with [TECHSPEC® Kinematic Mounts](#), [E-Series Kinematic Mounts](#), [Compact Mirror Mounts](#), and many other [optical mounts](#). M6 x 1.0 or 1/4"-20 tapped holes on the bottom surface make these Pedestal Posts directly mountable to Edmund Optics [stages](#) and [breadboards](#). For more compact table mounting, use the Compact Mounting Clamps ([#16-335](#)).

**Note:** Optical Mount Adapters are available to ensure consistent optical axis height and mounting hole compatibility with Edmund Optics' Optical Mounts. Refer to the Technical Information tab to find the right adapter for your application.

## Technical Information

PEDESTAL POSTS AND ACCESSORIES					
Compatible Optic Mount	Optical Size	Mount Stock Number	Extension Length (mm)	Extender Stock Number for English Pedestals	Extender Stock Number for Metric Pedestals
 <p><b>Optic Component Mount</b></p>	50mm Dia.	<a href="#">#64-567</a>	16.8	<a href="#">#16-321</a>	<a href="#">#16-315</a>
	2"/50.8mm Dia.	<a href="#">#64-569</a>	16.8	<a href="#">#16-324</a>	<a href="#">#16-587</a>
 <p><b>Bar-Type Lens / Filter Holder</b></p>	1"/25.4mm Dia	<a href="#">#03-676</a>	18	<a href="#">#16-325</a>	<a href="#">#16-588</a>
	2 axis: 2"/50.8mm Dia.	<a href="#">#62-957</a>	8	<a href="#">#16-317</a>	<a href="#">#16-311</a>
	3 axis: 1"/25.4mm Dia.	<a href="#">#62-959</a>	18	<a href="#">#16-222</a>	<a href="#">#16-316</a>
	5 axis: 1"/25.4mm Dia.	<a href="#">#13-776</a>	18	<a href="#">#16-222</a>	<a href="#">#16-316</a>
	2"/50.8mm Dia.	<a href="#">#03-669</a>	11	<a href="#">#16-323</a>	<a href="#">#16-586</a>
	2"/50.8mm Dia.	<a href="#">#55-530</a>	16	<a href="#">#16-320</a>	<a href="#">#16-314</a>
 <p><b>Multi-Axis Adjustable Optic Mounts</b></p>	2 axis: 1"/25.4mm Dia.	<a href="#">#62-956</a>	20.8	<a href="#">#16-460</a>	<a href="#">#16-459</a>

 <p><b>Rectangular Bar Clamp</b></p>	2"/50.8mm Sq.	#54-995	11	#16-318	#16-312
 <p><b>Filter Mount</b></p>	2"/50.8mm Sq.	#54-997	14	#16-319	#16-313
 <p><b>Multiple Filter Holder</b></p>	30mm Dia.	#55-006	16	#16-320	#16-314
 <p><b>Spring Mount Filter Holder</b></p>	2"/50.8mm Sq.	#55-531	16	#16-320	#16-314
 <p><b>Prism Mounts</b></p>	25mm Cube	#55-013	18	#16-322	#16-316
	50mm Cube	#53-027	18	#16-325	#16-588
 <p><b>Polarizer</b></p>	1"/25.4mm Dia.	#55-011	18	#16-322	#16-316
	2"/50.8mm Dia.	#56-329	8	#16-317	#16-311
 <p><b>Top Adjustment Kinematic Mount</b></p>	1"/25.4mm Dia.	#55-456	14	#16-319	#16-313
 <p><b>Gimbal Mount</b></p>	2"/50.8mm Dia.	#55-000	11	#16-318	#16-312