

TECHSPEC® S-Mount Kinematic Mount (3-Screw Adjustment)



S-Mount Kinematic Mount (3-Screw Adjustment) (#11-133)

Stock #11-133 **14 In Stock**

⊖ 1 ⊕ MRP ₹13,923

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-49	₹13,923 each
Qty 50+	₹13,247 each
Need More?	Request Quote

Product Downloads

General

Tube Mount **Type:**

Kinematic (Tip-Tilt) **Function:**

3 **Number of Adjustment Screws:**

Physical & Mechanical Properties

Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings	
19.60	Thickness (mm):
Z-Axis: 6	Travel (mm):
±5	Fine Tilt Angle (°):
±5	Fine Tip Angle (°):
7.0	Sensitivity per 1° Knob Rotation (arcsec):
0.20	Adjustment Screw Pitch (mm):
M12 x 0.5	Aperture Size:
23.5	Height (mm):
1.3	Pointing Accuracy (μrad):

Threading & Mounting

S-Mount	Thread Type:
M4	Mounting Threads:
M4 x 0.7	Compatible Post:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Allow for Kinematic Adjustment of C, S, and T-Mount Components
- Horizontal Mounting Adapters Available
- Removable Turning Knobs for Hex Key Access

TECHSPEC® C, S, and T-Mount Kinematic Mounts feature high accuracy adjustment screws in either two or three screw versions for control of tip and tilt. Three screw versions allow additional translation in the optical axis (Z-Axis). The C-Mount Kinematic Mounts have 1"-32 TPI female threading to hold C-Mount components; the S-Mount Kinematic Mounts have M12 x 0.5 threading to hold S-Mount components; the T-Mount Kinematic Mounts have M42 x 0.75 threading to hold T-Mount components. All three mounts use fine adjustment, 100+ TPI, screws to provide ±5° of tip/tilt, and high quality construction and materials ensure quality and repeatability. Stainless steel inserts are used for all adjustment screw contact surfaces and specially designed dampening grease provides smooth movement. Adjustment knobs are removable for Allen Key or motorized adjustment (2mm key size). TECHSPEC® C, S, and T-Mount Kinematic Mounts are designed to connect to our [TECHSPEC® Optical Posts](#). For C-Mount and T-Mount types, when the male-thread adapter is removed from the post, either an M4 or 8-32 tapped hole is available to accept the post-mounting screw from the mount. For the S-Mount types, an M4 hole is available for mounting.

Note: Included hardware kits contain appropriate post mounting screws and Allen wrenches for adjustment. [TECHSPEC® Optical Mount Accessories](#) are available to easily integrate TECHSPEC® C, S, and T-Mount Kinematic Mounts into a variety of applications.