

Smart Vision Lights 75mm Green Bar Light



Stock **#90-433** NEW **1 In Stock**

-

1

+

 ₹47,634

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹47,634 each
Need More?	Request Quote

Product Downloads

General	
LM75-530-W	Model Number:
LED Illuminator	Type of Illumination:
Note: 5-Pin M12 cables sold separately (5m #23-951, 10m #23-952, 15m #23-953) Industrial power supply for mounting to DIN rails also sold #75-579	
Smart Vision Lights LLC	Manufacturer:

Bar Light	Geometry:
Constant or Strobed	Illumination Mode:
Physical & Mechanical Properties	
80.00 L x 34.00 W x 26.00 D	Dimensions (mm):
256	Weight (g):
71.00 L x 25.5 W	Active Area (mm):
Optical Properties	
Green	Color:
530	Wavelength (nm):
100 - 1000	Working Distance (mm):
Electrical	
30 - ∞	Strobe Duration (µs):
Hardware & Interface Connectivity	
5-pin M12 connector	Connector:
24 VDC ± 5%	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #75-577 Europe: #75-578 Japan: #75-577 Korea: #75-579 China: #75-579	
Threading & Mounting	
T-Slot for M6 Nut	Mount:
Environmental & Durability Factors	
-10° to +40°	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Compact Bar Lights Available In 45mm Or 75mm Lengths
- Delivers up to 73,000 (for the 75mm) and 44,000 (45mm) lux with Strobing
- Available In White, Blue, Green, Red, Or IR Wavelengths
- Ideal For Space-Constrained Imaging Applications

Smart Vision Lights LMMini Bar Lights are compact linear lights that are designed to deliver intense light for space-constrained applications and feature IP65 rating for dust and water protection. These lights are available in 45 or 75mm lengths in white, blue (470nm), green (530nm), red (635), or IR (850nm) wavelengths. Built in Multi-Drive™ technology allows for these lights to operate in continuous mode for standard operation or strobe mode for high speed or increased brightness needs. Smart Vision Lights LMMini Bar Lights are recommended to use at a working distance of 100 – 1000mm. Optional mounting brackets are sold separately and can be used to configure the lights in a quad formation to illuminate a larger area.