

TECHSPEC<sup>®</sup> T-Mount, 60mm x 85mm Plate Mount, 1/4-20



Stock #65-982 4 In Stock

-

1

+

₹35,208

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹35,208 each                  |
| Qty 5-9        | ₹32,853 each                  |
| Qty 10-25      | ₹31,232 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                                  |                 |
|--------------------------------------------------------------------------|-----------------|
| Optic Mount (Fixed)                                                      | Function:       |
| Rectangular                                                              | Type of Optics: |
| Note:<br>Includes four T-Mount Aperture Caps ( <a href="#">#66-037</a> ) |                 |
| Dimensions of Compatible Optics (mm):<br>60.0 x 85.0                     |                 |

| Physical & Mechanical Properties    |                                           |
|-------------------------------------|-------------------------------------------|
| 75.0 x 75.0 x 75.0                  | Dimensions (mm):                          |
| 75.0                                | Extension Length (mm):                    |
| 1.0                                 | Min. Thickness of Compatible Optics (mm): |
| 7.1                                 | Max. Thickness of Compatible Optics (mm): |
| Threading & Mounting                |                                           |
| T-Mount                             | Thread Type:                              |
| 1/4-20                              | Compatible Post:                          |
| Regulatory Compliance               |                                           |
| Compliant                           | RoHS 2015:                                |
| View                                | Certificate of Conformance:               |
| Compliant                           | Reach 233:                                |
| China                               | Country of Origin:                        |
| Edmund Optics India Private Limited | Imported By:                              |

## Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

**Note:** #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

## Technical Information

