

TECHSPEC<sup>®</sup> T-Mount, 60mm x 85mm Plate Mount, M6



Stock **#65-983** 1 In Stock

-

1

+

₹35,208

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | ₹35,208 each                  |
| Qty 5-9        | ₹31,122 each                  |
| Qty 10-25      | ₹28,665 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

|                     |                 |
|---------------------|-----------------|
|                     | Function:       |
| Optic Mount (Fixed) |                 |
|                     | Type of Optics: |
| Rectangular         |                 |

|                                                                                 |  |
|---------------------------------------------------------------------------------|--|
| <b>Note:</b><br>Includes four T-Mount Aperture Caps ( <a href="#">#66-037</a> ) |  |
| <b>Dimensions of Compatible Optics (mm):</b><br>60.0 x 85.0                     |  |
| <b>Physical &amp; Mechanical Properties</b>                                     |  |
| <b>Dimensions (mm):</b><br>75.0 x 75.0 x 75.0                                   |  |
| <b>Extension Length (mm):</b><br>75.0                                           |  |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>1.0                         |  |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>4.73                        |  |
| <b>Threading &amp; Mounting</b>                                                 |  |
| <b>Thread Type:</b><br>T-Mount                                                  |  |
| <b>Compatible Post:</b><br>M6 x 1.0                                             |  |
| <b>Regulatory Compliance</b>                                                    |  |
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>                                  |  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a>                      |  |
| <b>Reach 233:</b><br><a href="#">Compliant</a>                                  |  |

PRODUCT DETAILS

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
  - Provides a 90° Mounting Interface
  - ¼"-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

TECHNICAL INFORMATION

