

[See all 186 Products in Family](#)

# VIS 25.4mm Dia Longpass Filter Kit

See More by [Hoya](#)



Stock #47-399 **2 In Stock**

- 1 + MRP ₹30,167

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹30,167 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Filters Included :  
[GG475](#), [GG495](#), [OG515](#), [OG530](#), [OG550](#), [OG570](#),  
[OG590](#), [RG610](#)

Type:  
Longpass Filter

### Physical & Mechanical Properties

Diameter (mm):  
25.40

Bevel:

Protective as needed

## Optical Properties

Colored Glass **Substrate:**

Uncoated **Coating:**

Multiple Colors **Color:**

VS **Wavelength:**

## Regulatory Compliance

**Compliant** **Reach 181:**

**Exempt** **RoHS 2015:**

**View** **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
 Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

## Product Details

- UV, VS and IR Pass Ranges
- VS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Hoya Colored Glass Longpass Filters feature a colored glass substrate. These filters are manufactured from substrates with inherently different absorption and transmission properties across a specific spectral region. Hoya Colored Glass Longpass Filters have UV, VS, and IR pass ranges. A longpass filter has low transmission in the shortwave region (stopband) and high transmission in the longwave region (passband). These filters are also available in a [mounted](#) version.

### Longpass Filter Kits

Longpass filter kits are available in three different options: UV-VIS, VS, or VS-NIR. Each kit contains 8 filters in either 12.5mm diameter, 1" diameter, or 2" square.

UV-VIS Kit Contains: WG 295, WG 305, WG 320, L 37, GG 400, GG 420, GG 435, GG 455

VS Kit Contains: GG 475, GG 495, OG 515, OG 530, OG 550, OG 570, OG 590, RG 610

VS-NIR Kit Contains: RG 630, RG 665, RG 695, RG 715, RG 780, RG 830, RG 850, RG 1000

### Complete Filter Kits


Complete filter kits are available with 12.5mm diameter, 50.0mm diameter, 1" diameter, or 2" square filters. Each kit contains all 37 Longpass Glass Color Filter types.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact [kits@edmundoptics.com](mailto:kits@edmundoptics.com).

## Filter Simulation Software

[Click here](#) to download HOYA's colored glass filter simulation software which can be used to calculate the internal transmittance and external transmission of each HOYA glass type. The software can simulate the performance of individual filters with user specified thickness.

## Technical Information



$\lambda_s$	limit of stopband: specified at 0.001% internal transmittance
$\lambda_c$	cut-off position: specified at 50% internal transmittance
$\lambda_p$	limit of the passband
$T_{ip}$	internal spectral transmittance at $\lambda_p$
$\rho$	density
$T_g$	transformation temperature