

[See all 16 Products in Family](#)

## White, Strobed, Brightfield/Darkfield LED Ring Light w/ Barrel Mount

See More by [Advanced Illumination](#)



Stock #83-249 **1 In Stock**

MRP ₹1,56,645

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | ₹1,56,645 each                |
| Need More? | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

|                |                              |
|----------------|------------------------------|
| RL5064B-WHI-IS | <b>Model Number:</b>         |
| 50,000         | <b>LED Lifetime (hours):</b> |
| 64.00          | <b>Number of LEDs:</b>       |
|                | <b>Type of Illumination:</b> |

**Note:**  
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination **Manufacturer:**

Ring Light **Geometry:**

Strobed **Illumination Mode:**

## Physical & Mechanical Properties

100.00 **Diameter (mm):**

33.7 **Height (mm):**

55.5 **Inner Diameter (mm):**

100.00 **Outer Diameter (mm):**

## Optical Properties

White **Color:**

6 - 64 **Working Distance (mm):**

## Electrical

30.00 **Maximum Trigger Frequency (Hz):**

30 - 300 **Strobe Duration (µs):**

## Hardware & Interface Connectivity

Flying Leads **Connector:**

**Power Supply:**  
Power Supply Required and Sold Separately:  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

## Threading & Mounting

Barrel Mount **Mount:**

M4 x4 **Mounting Threads:**

## Environmental & Durability Factors

0-65 **Operating Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 233:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

For more information on Darkfield Illumination, click [here](#).

- Hybrid Diffuse Brightfield and Darkfield Illumination
- Can Be Used Independently or Simultaneously
- Fixed Intensity or Strobed Options

Advanced Illumination Brightfield/Darkfield LED Ring Lights offer a level of versatility not previously available. Two independently powered rings of LEDs provide darkfield and brightfield illumination. The strobed models' flash duration is dependent on a trigger signal or potentiometer setting. The duration of the strobe can be adjusted from 30 - 300 $\mu$ s via a knob located in the back of the unit. The trigger input signal of the Advanced Illumination Brightfield/Darkfield LED Ring Light is CMOS/TTL compatible. The maximum trigger frequency is 30 Hz.

**Note:** Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

#### 3D-Printable Mount Files




Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.

#### Application Note

Illumination Mounts for Machine Vision Applications  
[Read](#) 

#### Video

Assembly of 3D Printed Mounts for Common Illumination Geometries  
[Watch](#) 