## NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

 COATING (APPLY ACROSS COATING APERTURE) \$1 & \$2: R(ABS) ≤1.0% FROM 250 - 425nm R(AVG) ≤0.75% FROM 250 - 425nm R(AVG) ≤0.5% FROM 370 - 420nm







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	]		P	Edmund Optic	<b>C</b> ®
SHAPE	PLANO	PLANO					
SURFACE ACCURACY	1λ	1λ	THIRD ANGLE PROJECTION		TITLE	40mm DIA. UV AR COATED, 1λ FUSED SILICA WINDOW	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø36.00	Ø36.00		<u> </u>		WINDOW	CHEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	45814	SHEET 1 OF 1

