


NOTES:


1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. CLEAR APERTURE AND COATING APERTURE
ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1: Ravg ≥90% @ 750 - 1150nm
Ravg ≥80% @ 1200 - 1600nm

S2:NONE



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2	Edmund Optics®			
SHAPE	PLANO	PLANO	25mm DIA., Extended Hot Mirror			
SURFACE QUALITY	80-50	80-50				
SURFACE FLATNESS	4 - 6λ	4 - 6λ	THIRD ANGLE PROJECTION		TITLE	46386
CLEAR APERTURE	Ø22.5	Ø22.5	ALL DIMS IN mm		DWG NO	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	SHEET 1 OF 1			