


NOTES:


- 1. ALLOWABLE OPTICAL MATERIAL:
OPTICAL GRADE GERMANIUM
UNCOATED TRANSMISSION >45% AT 4 MICRONS
FOR 5mm THICK SAMPLE
- 2. CENTERING TOLERANCE:
BEAM DEVIATION: <3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. DIAMOND TURNED

- 5. FOCAL LENGTH TOLERANCE: $\pm 1\%$



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

	S1	S2	EFL (AT 10.6 microns)	30.00	 Edmund Optics®	
SHAPE	CONVEX	PLANO				
RADIUS	90.12	INFINITY	BFL (AT 10.6 microns)	29.25	TITLE	Ge Plano-Convex Lens, 25mm Dia. x 30mm FL, Uncoated
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	Ø 24	Ø 24				
BEVEL MAX FACE	0.3mm x 45°	0.3mm x 45°	ALL DIMS IN	mm	DWG NO	69638
						SHEET 1 OF 1