



NOTES:

- 1. SUBSTRATE MATERIAL: GRADE A FINE ANNEALED SCHOTT: BOROFLOAT® 472/657
- 2. COATING (APPLY ACROSS CLEAR APERTURE) SPECIFICATIONS APPLY FOR 45° AOI
 - S1: T(AVG) > 85% FROM 400-690nm
 - R(AVG) > 95% FROM 750-1125nm
 - R(ABS) > 90% FROM 800-1050nm
- S2: R(AVG) < 1.0% FROM 400-700nm
- 3. EDGES: CUT, SHARP EDGES REMOVED



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			EFL (AT 587.6nm)	NA	 Edmund Optics®		
	S1	S2					
SHAPE	PLANO	PLANO					
SURFACE ACCURACY AT 632.8nm (P-V)	4-6 WAVES PER INCH	4-6 WAVES PER INCH	BFL (AT 587.6nm)	NA	TITLE	45° AOI, 20mm Square, Hot Mirror	
SURFACE QUALITY	80 - 50	80 - 50					
MIN CLEAR APERTURE	19.00 x 19.00	19.00 x 19.00	ALL DIMS IN	mm	DWG NO	64466	SHEET 1 OF 1