


NOTES:

1. SUBSTRATE:  
FUSED SILICA MOUNTED IN BLACK ANODIZED ALUMINUM RING
2. TRANSMITTED WAVEFRONT ERROR:  $\lambda/4$
3. RoHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



|                                 | VALUE                     |
|---------------------------------|---------------------------|
| CENTER WAVELENGTH (CWL) (nm)    | 386 ± 3                   |
| MINIMUM BANDWIDTH (nm)          | 23                        |
| FULL WIDTH HALF MAX (FWHM) (nm) | 27                        |
| MINIMUM TRANSMISSION (%)        | >90                       |
| OD6 BLOCKING RANGE (nm)         | 410 - 510                 |
| SURFACE QUALITY                 | 60-40                     |
| COATING TYPE                    | HARD COATED               |
| DURABILITY                      | MIL-C-48497A, SECT. 3.4.1 |
| ENVIRONMENTAL                   | MIL-STD-801F, SECT. 507.4 |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**Edmund Optics®**



ALL DIMS IN

mm

TITLE

OD6, Ø25mm, 386nm x 27nm, BP  
FLUORESCENCE FILTER

DWG NO

33321

SHEET  
1 OF 1