



NOTES:

1. SUBSTRATE:
FUSED SILICA MOUNTED IN BLACK ANODIZED ALUMINUM RING
2. TRANSMITTED WAVEFRONT ERROR: $\lambda/4$
3. RoHS: COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



	VALUE
CENTER WAVELENGTH (CWL) (nm)	530 ± 3
MINIMUM BANDPATH (nm)	55
FULL WIDTH HALF MAX (FWHM) (nm)	62
MINIMUM TRANSMISSION (%)	>93
OD6 BLOCKING RANGE (nm)	400 - 485 & 569 - 750
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48497A, SECT. 3.4.1
ENVIRONMENTAL	MIL-STD-801F, SECT. 507 .4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	OD6, Ø12.5mm, 530nm x 55nm, BP FLUORESCENCE FILTER	
ALL DIMS IN	mm	DWG NO	87736	SHEET 1 OF 1