

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



NOTES:

1. SUBSTRATE
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 arcsec
3. COATING (APPLY ACROSS COATING APERTURE)
ENVIRONMENTAL DURABILITY:
PHYSICAL DURABILITY:
PERFORMANCE SPECIFICATIONS:
T(avg):>85% FROM 325 - 480nm FOR RANDOM POLARIZATION @ 45° AOI
T(abs): >85% FROM 325 - 480nm FOR ALL POLARIZATION @ 45° AOI
R(avg):>97% FROM 520 - 610nm FOR RANDOM POLARIZATION @ 45° AOI
R(abs): >97% FROM 520 - 610nm FOR ALL POLARIZATION @ 45° AOI
T(abs): = 50% 500nm @ 45° AOI

S1: HARD COATED
S2: SINGLE LAYER MgF2



4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE
6. TRANSMITTED WAVEFRONT DISTORTION RMS@ 632.8nm $\leq \frac{1}{4} \lambda$
7. ROHS COMPLIANT



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	<div>TITLE</div>	500nm, 25.2 x 35.6mm,DICHROIC SHORTPASS FILTER		
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	22.0 x 32.0	22.0 x 32.0					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	69214	SHEET 1 OF 1