





NOTES:


1. SUBSTRATE:  
HOYA GLASS: ND-40
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <0.02 mm
3. FINE GRIND SURFACE
4. OPTICAL DENSITY: 0.4 ±0.05
5. TRANSMISSION (%): 40 % AVERAGE FROM 400-700nm
6. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                 |                      |                      |                                                                                                              |    |        |                                      |                 |
|-----------------|----------------------|----------------------|--------------------------------------------------------------------------------------------------------------|----|--------|--------------------------------------|-----------------|
|                 | S1                   | S2                   | THIRD ANGLE PROJECTION  |    | TITLE  | OD 0.4, Ø12.5mm ABSORPTIVE ND FILTER |                 |
| SHAPE           | PLANO                | PLANO                |                                                                                                              |    |        |                                      |                 |
| SURFACE QUALITY | 80-50                | 80-50                | ALL DIMS IN                                                                                                  | mm | DWG NO | 48525                                | SHEET<br>1 OF 1 |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |                                                                                                              |    |        |                                      |                 |