




NOTES:

- 1. SUBSTRATE : ZINC SELENIDE (ZnSe)
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: UNCOATED  
S2: UNCOATED

3. FINE GRIND SURFACE



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
CLEAR APERTURE	85%	85%
ANGLE TOL. (arcmin)	±10	±10
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	2λ	2λ
WAVELENGTH RANGE (nm)	600 - 18000	600 - 18000
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

ZINC SELENIDE, 25.4mm, UNCOATED, IR RIGHT ANGLE PRISM

DWG NO

64123

SHEET

1 OF 1