## NOTES:

1. SUBSTRATE: FLOAT GLASS

2. ANTI REFLECTION SURFACE TREATMENT (APPLY ACROSS CLEAR APERTURE)


AOI: 0


S1 & S2: Ravg ≤0.5% @ 425 - 700nm



4. ROHS COMPLIANT







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
CLEAR APERTURE	≥90%	≥90%			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

THIRD ANGLE _ PROJECTION		TITLE	Ø101.6n
ALL DIMS IN	mm	DWG NO	46104

TITLE	Ø101.6mm x 3mm HIGH EFFICIENCY WI	NDOW
DWG NO	4/104	SHEET

**Edmund Optics®** 

1 OF 1