




- NOTES:
- 1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
 $R(ABS) \leq 0.25\% @ 266nm$
 - 2. RoHS: COMPLIANT




M30 x 1

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	1.5J/cm ² @ 10ns, 20Hz, 266nm
DESIGN WAVELENGTH DWL (nm)	266
EXPANSION POWER	2X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	< $\lambda/10$ FOR 4mm INPUT BEAM (NOMINAL)

THIRD ANGLE
PROJECTION



ALL DIMS IN mm

Edmund Optics®

TITLE

2X, 266nm VEGAT™ Nd:YAG LASER LINE BEAM
EXPANDER

DWG NO

35092

SHEET
1 OF 1