




NOTES:

1. CENTERING TOLERANCE (AT 587.6nm):  
BEAM DEVIATION (HALF ANGLE): < 10.0 arcmin
2. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE

△ 3 OVERCOAT SURFACES USING INCONEL AND BLACK PAINT





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	9.00 x 9.00	1mm FROM EDGES

2	1	47259	10mm ALUMINIZED, SCHMIDT PRISM
1	1	65587	PECHAN PRISM, 10mm
ITEM	QTY	PART NUMBER	Description

		 <b>Edmund Optics®</b>	
THIRD ANGLE PROJECTION 		TITLE	10.0mm, SCHMIDT-PECHAN PRISM
ALL DIMS IN	mm	DWG NO	36038
			SHEET 1 OF 1