



NOTES:

1. SUBSTRATE MATERIAL
SCHOTT: N-BK7 517/642
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NIR I
Ravg ≤ 0.5% @ 600 - 1050nm

3. FINE GRIND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL.	±15	±15
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm



TITLE	12.5mm, NIR I COATED, BBAR COATED RIGHT ANGLE PRISM	
DWG NO	84523	SHEET 1 OF 1