## NOTES:


- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE) SURFACE MARKED G: NONE SURFACE MARKED S1, S2, S4 & S5: R(avg) <0.25% @ 1064nm @ 0° AOI


SURFACE MARKED S3: NON-POLARIZING COATING PER FINISHED CUBE SPECIFICATIONS LISTED BELOW

4. APPLY MARK IDENTIFYING BEAMSPLITTER COATED RIGHT ANGLE PRISM WITH PENCIL OR PERMANENT INK

5. TOLERANCES:

S1 & S2 BEAM DEVIATION TO BE WITHIN 2 arcmin S4 & S5 BEAM DEVIATION TO BE WITHIN 2 arcmin





## *FOR INFORMATION ONLY:* DO NOT MANUFACTURE PARTS TO THIS DRAWING

## SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

AVERAGE TRANSMISSION	45% ± 5% <3%				Edmund Optic	CS <sup>®</sup>
ABSOLUTE TRANSMISSION	45% ± 10%			TITLE	12.5mm, 1064nm, NON-POLARIZING CUBE BEAMSPLITTER	
SURFACE FLATNESS	λ/8					
SURFACE QUALITY	40-20		•			SHEET
CLEAR APERTURE	90 %	ALL DIMS IN	mm	DWG NO	35965	1 OF 1