




NOTES:

- 1. SUBSTRATE:
Fused Silica (Corning 7980)
- 2. TEMPERATURE RANGE:
-40 TO +170 °C

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE (mm)	Ø 21.6 ± 0.1
DIFFUSING ANGLE	2 ± 1.5°
TRANSMISSION EFFICIENCY	90%

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

EO[®] Edmund Optics[®]

TITLE	15° DIFFUSING ANGLE 25mm DIA., UV HOLOGRAPHIC DIFFUSER		
DWG NO	48507	SHEET 1 OF 1	