


NOTES:



- 1. SUBSTRATE:
D-ZK3
- 2. NUMERICAL APERTURE: 0.43
- 3. COATING
S1 & S2: R(AVG) ≤ 0.5% @ 350 - 700nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.070



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY			EFL	4.5	 Edmund Optics®		
	S1	S2	BFL	2.19			
SHAPE	CONVEX	PLANO			TITLE	0.43 NA 4.50mm FL 350-700nm AR Coated, Molded Aspheric Lens	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø3.65	Ø3.65					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			ALL DIMS IN	mm	DWG NO