




NOTES:

- 1. SUBSTRATE:  
L-LAL12
- 2. NUMERICAL APERTURE: 0.66
- 3. COATING  
S1 & S2: R(ABS) < 1.0% @ 350 - 500nm
- 4. FOCAL LENGTH TOLERANCE: ±1%
- 5. TRANSMITTED WAVEFRONT ERROR (λ, RMS): < 0.300



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	2.54	 <b>Edmund Optics®</b>		
			BFL	1.55			
SHAPE	CONVEX	PLANO		TITLE	405, 0.66 NA, BBAR COATED, ASPHERIC LENS		
SURFACE QUALITY	40 - 20	40 - 20					
CLEAR APERTURE	$\varnothing 3.30$	$\varnothing 3.30$					
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	83677	SHEET 1 OF 1