




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SUBSTRATE	Fused Silica
ANGLE OF INCIDENCE	0 ±2
BANDWIDTH (nm)	>1000
CENTER WAVELENGTH CWL (nm)	980
OPTICAL DENSITY OD	≥6.0
SHAPE	PLANO
SURFACE QUALITY	60-40
TRANSMISSION (%)	93
EDGE STEEPNESS (nm)	4.9
TRANSITION WIDTH (nm)	<9.8
CLEAR APERTURE (%)	>80
DURABILITY	Environmental: MIL-STD-810F, Physical: MIL-C-48497A
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	25mm Dia., 980nm Laser Line Longpass Filter	
ALL DIMS IN	mm	DWG NO	47509	SHEET 1 OF 1