





NOTES:


- 1. SUBSTRATE:
α-BBO
- 2. BEAM DEVIATION: <3 arcmin
- 3. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

WAVEFRONT DISTORTION	$\lambda/2$ @ 632.8 nm
DAMAGE THRESHOLD, PULSED	2 J/cm ² , 10ns, 10 Hz @ 1064 nm
WAVELENGTH RANGE (nm)	200 - 350
SURFACE QUALITY	20-10
EXTINCTION RATIO	< 0.000005

THIRD ANGLE PROJECTION 	
ALL DIMS IN	mm

			
TITLE	GLAN-TAYLOR POLARIZER 200 - 350nm, 8mm		
DWG NO	89549	SHEET 1 OF 1	