NOTES:

 SUBSTRATE MATERIAL: SCHOTT: N-BK7


2. CENTERING TOLERANCE (AT 587.6nm)
BEAM DEVIATION: ±3 arc min.


3. COATING (APPLY ACROSS CLEAR APERTURE)
S1, S2, S3 & S4: λ/4 MgF2 @ 550nm ON FACES
S5: MULTILAYER DIELECTRIC TO ACHEIVE

 $R(ABS) = 30\% \pm 5\% @ 550nm$ $T(ABS) = 70\% \pm 5\% @ 550nm$ $R(AVG) = 30\% \pm 10\% FROM 400 - 700nm$ $T(AVG) = 70\% \pm 10\% FROM 400 - 700nm$

fine ground surface

5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	Edmund	Optics®

REV. A			1		5mm 30R/70T STANDARD CUBE BEAMSF	PLITTER
SURFACE FLATNESS	λ/4	THIRD ANGLE PROJECTION		TITLE	GITHIT GORY / GT ST/ KIND/ KID GODE DE/ KINDI EITTE	
SURFACE QUALITY	60-40		1			CHEET
CLEAR APERTURE	90%	ALL DIMS IN	mm	DWG NO	68545	SHEET 1 OF 1