



NOTES:

- COATING (APPLY ACROSS COATING APERTURE)  
 DUV Enhanced Aluminum (150-11000nm)  
 R(AVG) >83% @ 150 - 1000nm  
 R(AVG) >94% @ 1000 - 11000nm



SECTION A-A

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO  
 CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR  
 REFERENCE ONLY



THIRD ANGLE PROJECTION		TITLE	Infinite Conjugate, DUV Coated, 10X/0.22NA RefIX Objective	
ALL DIMS IN	mm	DWG NO	89722	SHEET 1 OF 1