


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



FOCAL LENGTH FL (mm)	1
MAGNIFICATION	200X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.62
WORKING DISTANCE (mm)	13
LENGTH EXCLUDING THREADS (mm)	82
MAXIMUM DIAMETER (mm)	34
TYPE	Microscope Objective
COMPATIBLE TUBE LENS	Focal Length: 200mm
DEPTH OF FOCUS (μm)	0.7
ENTRANCE PUPIL (mm)	0
FIELD OF VIEW, 1/2" SENSOR	0.03 x 0.025mm
FIELD OF VIEW, 18 DIAMETER FIELD EYEPiece (mm)	0.09
FIELD OF VIEW, 2/3" SENSOR	0.04 x 0.034mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPiece (mm)	0.12
RESOLVING POWER (μm)	0.4
WAVELENGTH RANGE (nm)	435 - 655
RoHS	Exempt

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



THIRD ANGLE
PROJECTION

TITLE

200X Mitutoyo Plan Apo SL Infinity Corrected
Objective

DWG NO

56072

SHEET
1 OF 1

ALL DIMS IN

mm