



NOTES:

- 1. SUBSTRATE
Polymer Film
- 2. INDEX OF REFRACTION nd:
Visible (Sodium D Line): 1.52
8-14µm: 1.53
15µm+: 1.48
- 3. COLOR: White
- 4. SHORE HARDNESS
D60-70
- 5. FLEXURAL MODULUS (psi)
(100-260) x 10³
- 6. YOUNGS MODULUS (psi)
(60-180) x 10³
- 7. COEFFICIENT OF THERMAL EXPANSION (10-6/°C)
11-13
- 8. OPERATING TEMPERATURE: 100°C
- 9. WAVELENGTH RANGE: 8000 - 14,000 nm
- 10. ROHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	24" x 24" White, IR Material Window
ALL DIMS IN	in	DWG NO	88611
			SHEET 1 OF 1