





FOCAL LENGTH (EFL): 100 ±1
BACK FOCAL LENGTH (BFL): 97,17

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	51,68±0,052 CX		GLASS N-BK7 517/642	R	∞ PL	
Øe	24			Øe	24	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				25,0mm Dia, x 100,0mm FL Uncoated, Plano-Convex Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	32481
			SHEET SIZE			SHEET
			A4			1 OF 1