




FOCAL LENGTH (EFL): $150 \pm 1,5$
 BACK FOCAL LENGTH (BFL): 147

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$153,49 \pm 0,153$ CX	GLASS N-BK7 517/642	R	$153,49 \pm 0,153$ CX
Øe	49		Øe	49
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

50mm Dia, x 150mm FL Uncoated,
Double-Convex Lens

DWG NO

32982

SHEET SIZE
A4

SHEET
1 OF 1