




FOCAL LENGTH (EFL): 72 ±0,72
 BACK FOCAL LENGTH (BFL): 70,29

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	33,01±0,033 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12mm Dia x 72mm FL, Uncoated, UV
 Plano-Convex Lens

DWG NO

36684

SHEET SIZE
 A4

SHEET
 1 OF 1