





FOCAL LENGTH (EFL): $27 \pm 0,27$
 BACK FOCAL LENGTH (BFL): $25,35$

- 1 VIS-NIR
 $R(\text{ABS}) \leq 0,25\%$ AT 880nm @ 0° AOI
 $R(\text{AVG}) \leq 1,25\%$ FROM $400\text{-}870\text{nm}$ @ 0° AOI
 $R(\text{AVG}) \leq 1,25\%$ FROM $890\text{-}1000\text{nm}$ @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 13,95 CX			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL		
Øe 8,1				Øe 8,1		
λ SEE NOTE 1				λ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,93'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 9,0mm Dia, x 27,0mm FL, VIS-NIR Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	45478
			SHEET SIZE			A4
			SHEET 1 OF 1			