




FOCAL LENGTH (EFL): 150 ± 1,5
 BACK FOCAL LENGTH (BFL): 148,37

1 AR COATING: VIS 0°
 R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	136,957±0,137 CX	GLASS FUSED SILICA 458/678	R	136,957±0,137 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®							
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm										
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE25mm Dia, x 150mm FL, VIS 0 Coated, UV Double-Convex Lens							
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING												
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:		mm		DWG NO48988		SHEET SIZE A4		SHEET 1 OF 1	