




FOCAL LENGTH (EFL): $9 \pm 0,09$

BACK FOCAL LENGTH (BFL): 7,12

- 1 AR COATING: UV-VIS
 $R(\text{AVG}) \leq 1,5\%$ FROM 250-700nm @ 0° AOI
 $R(\text{ABS}) \leq 1,0\%$ FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	7,39±0,007 CX	GLASS FUSED SILICA 458/678	R	7,39±0,007 CX
Øe	8,1		Øe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	6,55'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
SCALE: NONE
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

9mm Dia, x 9mm, UV-VIS Coated, UV Double-Convex Lens

DWG NO

49257

SHEET SIZE
A4

SHEET
1 OF 1