




FOCAL LENGTH (EFL):  $12 \pm 0,12$

BACK FOCAL LENGTH (BFL): 10,6

- 1 AR COATING: VIS-NIR  
 $R(ABS) \leq 0,25\%$  AT 880nm @ 0° AOI  
 $R(AVG) \leq 1,25\%$  FROM 400-870nm @ 0° AOI  
 $R(AVG) \leq 1,25\%$  FROM 890-1000nm @ 0° AOI

| LEFT SURFACE |                            | MATERIAL             | RIGHT SURFACE |                            |
|--------------|----------------------------|----------------------|---------------|----------------------------|
| R            | $9,42 \pm 0,009$ CX        | GLASS N-SF11 785/258 | R             | $\infty$ PL                |
| Øe           | 8,1                        |                      | Øe            | 8,1                        |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                      | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                      | 4/            | 1,27'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                      | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                      | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



**Edmund Optics®**

TITLE 9,0mm Dia, x 12,0mm FL, VIS-NIR Coated, Plano-Convex Lens

DWG NO 49915

SHEET SIZE A4

SHEET 1 OF 1