




FOCAL LENGTH (EFL): $2 \pm 0,02$

BACK FOCAL LENGTH (BFL): 1,57

1 AR COATING:

$\frac{1}{4}$ WAVE MgF2 @ 550nm
R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$1,7 \pm 0,002$ CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	1		Øe	1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 1,5mm Dia, x 2,0mm FL, MgF2 Coated, Plano-Convex Lens

DWG NO 65263

SHEET SIZE A4

SHEET 1 OF 1