






FOCAL LENGTH (EFL): $2 \pm 0,02$
 BACK FOCAL LENGTH (BFL): 1,57

1 AR COATING: VIS 0°
 $R(AVG) \leq 0,4\%$ FROM 425-675nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$1,7 \pm 0,002$ CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	1,5		Øe	1,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®										
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm													
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						TITLE				2,0mm Dia, x 2,0mm FL, VIS 0 Coated, Plano-Convex Lens					
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						DWG NO				65281		SHEET SIZE		SHEET	
INDICATIONS IN ACCORDANCE WITH ISO 10110				ALL DIMS IN:		mm						A4		1 OF 1	