




FOCAL LENGTH (EFL): 60 ±0,6

BACK FOCAL LENGTH (BFL): 58,65

- 1 AR COATING: NIR II  
R(ABS) ≤ 1,5% FROM 750-800nm @ 0° AOI  
R(ABS) ≤ 1,0% FROM 800-1550nm @ 0° AOI  
R(AVG) ≤ 0,7% FROM 750-1550nm @ 0° AOI

| LEFT SURFACE |                          | MATERIAL            | RIGHT SURFACE |                          |
|--------------|--------------------------|---------------------|---------------|--------------------------|
| R            | 31,11±0,031 CX           | GLASS N-BK7 517/642 | R             | ∞ PL                     |
| Øe           | 14                       |                     | Øe            | 14                       |
| 3/           | 3 (0,5) λ=632,8 nm       |                     | 3/            | 3 (0,5) λ=632,8 nm       |
| 4/           | -                        |                     | 4/            | 1,93'                    |
| 5/           | 40 - 20 (MIL-PRF-13830B) |                     | 5/            | 40 - 20 (MIL-PRF-13830B) |
| 6/           | -                        |                     | 6/            | -                        |


PROTECTIVE CHAMFERS AS NEEDED

ROHS:  
COMPLIANT

SCALE:  
NONE

λ = 587,6nm

FIRST ANGLE  
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT  
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE  
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS  
IN:

mm

TITLE

15,0mm Dia, x 60,0mm FL, NIR II Coated,  
Plano-Convex Lens

DWG NO

67522

SHEET SIZE  
A4

SHEET  
1 OF 1