





FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): $15,61$

1 AR COATING: YAG-BBAR
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$
 $R(AVG) < 1,0\% FROM 500-1100nm @ 0^\circ AOI$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$12,11 \pm 0,012 CX$	GLASS N-SF5 673/322	R	∞PL
Øe	14		Øe	14
3/	3 (0,5) $\lambda=632,8 nm$		3/	3 (0,5) $\lambda=632,8 nm$
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587,6nm$			TITLE	15,0mm Dia, x 18,0mm FL, YAG-BBAR Coated Plano-Convex Lens	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm		DWG NO	88853	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				INDICATIONS IN ACCORDANCE WITH ISO 10110			