


NOTES:


1. TYPE OF MOVEMENT: Rotary
TRAVEL (°): 360
2. TYPE OF DRIVE: Ultrasonic Motor
3. LOAD CAPACITY (kg): 1 (Horizontal)
4. RESOLUTION (°): 0.0022 Typ. (Open Loop)
5. WOBBLE (um): 100
FLATNESS (um): 5.0
ECCENTRICITY (um): 100
6. SPEED (°/s): 6 Max with #88-552
7. REPEATABILITY (°): Bi-directional: 0.0044 Uni-directional: 0.013
8. NOTE - Use with Piezo Positioning Stage Controller #88-552



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	Rotary Piezo Positioning Stage	
ALL DIMS IN	mm	DWG NO	88551	SHEET 1 OF 1